SPEAKMAN[®]

Eyesaver® Laboratory Single Lever Faucet with Integrated Eyewash

EYEWASH FEATURES:

- · Independent water channel for eyewash
- Brass spindle valve
- Pull handle activation
- Aerated yellow plastic spray outlets with integral flow control and flip-top dust caps
- 2.6 GPM (9.8 L/min) @ 30 PSI flow rate
- 1/2" NPT male inlet

FAUCET FEATURES:

- Brass construction with polished chrome finish
- Gooseneck spout with independent water channel for faucet
- Single handle lever with color-coded index
- Ceramic Cartridge
- Adjustable center of 4" to 6"
- 1.2. GPM (4.5 L/min) Flow Rate
- 3/8" compression male threaded inlet hose

EYEWASH OPTIONS:

• NA: Non-aerated eyewash outlets

FAUCET OPTIONS:

- 8: 8" Gooseneck spout for faucet
- BO: 0.5 GPM (1.89 L/min) faucet flow control
- FP: foot pedal for faucet operation (Not NSF 61/372 compliant)
- LF: 1.5 GPM (5.7 L/min) laminar faucet flow control
- ST: Serrated tip for faucet with vacuum breaker (Not NSF 61/372 compliant)
- TW: Thermostatic mixing valve for tepid water during eyewash usage

STANDARDS:

- ANSI/ISEA Z358.1 certified
- ASME A112.18.1/CSA B125.1 certified
- IGC 272 certified
- NSF/ANSI 61 certified
- NSF 372 certified

WARRANTY:

Visit www.speakman.com for full product warranty information

• 3 Year Limited Warranty (commercial)





Information continues on next page

ENSURE YOU ARE ANSI/ISEA Z358.1 Tepid Water Compliant by incorporating Speakman's 9.7 GPM Thermostatic Mixing Valve. -TW OPTION: Add the -TW



- suffix to the part number, this product ships complete with the TMV and connections
- STW-370: Thermostatic Mixing Valve (valve only)
- **SEF-TW:** Thermostatic Mixing Valve with necessary connections for SEF products

All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice


P: 800-537-2107


F: 800-977-2747

W: WWW.SPEAKMAN.COM

R: 03-NOVEMBER 2023

Eyesaver® Laboratory Single Lever Faucet with Integrated Eyewash





SEF-1800-CA-SL Spray Plume Length and Flow

SET 1000 CA SE Spray Frame Length and From										
Па	Flowing Pressure	30 psi	40 psi	50 psi	60 psi	70 psi	80 psi			
FIO		2.07 Bar	2.76 Bar	3.45 Bar	4.14 Bar	4.83 Bar	5.52 Bar			
	Flow Rate	2.9 gpm	3.1 gpm	2.9 gpm	2.9 gpm	2.9 gpm	2.9 gpm			
		11.09 L/min	11.55 L/min	11.13 L/min	10.98 L/min	10.90 L/min	10.86 L/min			
Eye	vewash Distance Plume "A"	13.5"	14.25"	14.25"	13.75"	13.75"	13.75"			
		34.29 cm	36.2 cm	36.2 cm	34.93 cm	34.93 cm	34.93 cm			

SEF-1800-CA-SL-8 Spray Plume Length and Flow

ozi 1000 ortoz o opray i famo zongar ana i for											
Flowing Pressure	30 psi	40 psi	50 psi	60 psi	70 psi	80 psi					
Flowing Pressure	2.07 Bar	2.76 Bar	3.45 Bar	4.14 Bar	4.83 Bar	5.52 Bar					
Flow Rate	2.9 gpm	3.1 gpm	2.9 gpm	2.9 gpm	2.9 gpm	2.9 gpm					
Flow Rate	11.09 L/min	11.55 L/min	11.13 L/min	10.98 L/min	10.90 L/min	10.86 L/min					
Eyewash Distance	17.0"	18"	17.5"	17.0"	17.0"	17.0"					
Plume "A"	43.18 cm	45.72 cm	44.45 cm	43.18 cm	43.18 cm	43.18 cm					

All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice.